



# D-A COARSE

## WOOL POLISHING PAD

The D-A COARSE wool pad is constructed using two distinct fiber lengths creating a dual density wool surface and a specific visible pattern. More than just an aesthetic detail, this configuration provides a great balance of cutting power and finishing ability when compared to traditional or single density wool pads.

### CUT/GLOSS



### TIPS FOR SUCCESS

- Always prime the pad by applying a thin, even layer of compound over the entire face before use
- Use small amounts to reload the pad
- Over-saturating the pad with compound can lead to diminished performance
- Clean pads frequently during use with compressed air, a vacuum, or RUPES Claw Pad Tool to maintain consistent performance

### RECOMMENDED COMPOUNDS

#### D-A COARSE



#### MILLE COARSE



#### MILLE COARSE BLACK LINE





#### XC-2



### RECOMMENDED POLISHERS

**Random orbital Polishers:** iBrid Series (HLR 21-15, HLR75 Mini, Nano) LHR21 Series, LHR15 Series, LHR75E Mini, LHR12E Duetto  
**Gear Driven:** LK900E



PADS CODES	SIZES
9.BW40H	Ø30-45mm (1" - 1.5") for iBrid nano
9.BW70H	Ø50-65mm (2" - 2.5") for iBrid nano
9.NW80H	Ø80-90mm (3" - 3.5")
9.NW130H	Ø130-145mm (5" - 5.7")
9.NW160H	Ø150-170mm (6" - 6.75")

### INDUSTRIES & APPLICATIONS

