




# D-A MEDIUM WOOL POLISHING PAD

The D-A MEDIUM wool Pad is composed by a soft and flexible wool, paired with a soft and flexible yellow foam backing and provides excellent cutting of moderate defects, excellent finishing ability on most surfaces.



► **TIPS FOR SUCCESS**


- Always prime the pad by applying a thin, even layer of compound over the entire face before use
- Use small amounts to reload the pad
- Over-saturating the pad with compound can lead to diminished performance
- Clean pads frequently during use with compressed air, a vacuum, or RUPES Claw Pad Tool to maintain consistent performance

► **RECOMMENDED COMPOUNDS**



► **RECOMMENDED POLISERS**

**Random orbital Polishers:** iBrid Series (HLR 21-15, HLR75 Mini, Nano) LHR21 Series, LHR15 Series, LHR75E Mini, LHR12E Duetto  
**Gear Driven:** LK900E



| PADS CODES | SIZES                               |
|------------|-------------------------------------|
| 9.BW40M    | Ø30-45mm (1" - 1.5") for iBrid nano |
| 9.BW70M    | Ø50-65mm (2" - 2.5") for iBrid nano |
| 9.NW80M    | Ø80-90mm (3" - 3.5")                |
| 9.NW130M   | Ø130-145mm (5" - 5.7")              |
| 9.NW160M   | Ø150-170mm (6" - 6.75")             |



**INDUSTRIES & APPLICATIONS**

